



SPA-04



SPA-08



SPA-16



SPA-32



SPA-64



INTRODUCTION

- ◆ Single/dual input for choice, built in optical switch for dual input, the switching power can be set by the button in the front panel or by web SNMP.
- ◆ Output adjustable by buttons in the front panel or web SNMP, the range is down 4dBm
- ◆ Maintenance function of one-time downward attenuation of 6dBm by buttons in the front panel or web SNMP, to facilitate the optical fiber hot-plug operation without turn off the device
- ◆ Multi- ports output, can built in 1310/1490/1550WDM.
- ◆ Standard RJ 45 port for remote control, we can provide output contract and web manager for choice, and also plug-in SNMP hardware can be reserved for update.
- ◆ With laser key to turn on/off the laser.
- ◆ With RF test function.
- ◆ Adopts JDSU or Oclaro Pump laser
- ◆ Led displays the working condition of the machine
- ◆ Dual power hot plug power supply for choice, 90V~250V AC or -48V DC

| Items | Parameter | | | | | | | | | |
|------------------------------------|-------------------------------------|------|---------------------|------|---------------------|------|---------------------|------|----------------------|-------|
| Output (dBm) | 31 | 32 | 33 | 34 | 35 | 36 | 37 | 38 | 39 | 40 |
| Output (mW) | 1250 | 1600 | 2000 | 2500 | 3200 | 4000 | 5000 | 6400 | 8000 | 10000 |
| Input(dBm) | -8~+10 | | | | | | | | | |
| Output Port Number | 4 | | 8 | | 16 | | 32 | | 64 | |
| Range of output adjustment (dBm) | Down 4 | | | | | | | | | |
| one-time downward attenuation(dBm) | Down 6 | | | | | | | | | |
| Wavelength (nm) | 1540~1565 | | | | | | | | | |
| Output stability(dB) | <±0.3 | | | | | | | | | |
| Optical Return Loss (dB) | ≥45 | | | | | | | | | |
| Fiber Connector | FC/APC、SC/APC、SC/IUPC、LC/APC、LC/UPC | | | | | | | | | |
| Noise Figure (dB) | <6.0(input 0dBm) | | | | | | | | | |
| Web port | RJ45(SNMP) | | | | | | | | | |
| Power Consumption (W) | ≤80 | | | | | | | | | |
| Voltage (V) | 220VAC(90~265)、-48VDC | | | | | | | | | |
| Working Temp (°C) | -0~55 | | | | | | | | | |
| Size (mm) | 370(L)×486(W)×45(H) | | 370(L)×484(W)×48(H) | | 370(L)×484(W)×48(H) | | 370(L)×484(W)×48(H) | | 370(L)×484(W)×132(H) | |
| NW (Kg) | 8 | | 10 | | 12 | | 14 | | 18 | |